

Off-The-Shelf Mizu-P25 (Mini Type) Cable Assemblies

molex

Off-The-Shelf Mizu-P25 (Mini Type) Cable Assemblies
feature 2.50mm pitch, up to 4.0A current and an IP67 rating with a variety of cable lengths

Features and Advantages

Positive lock

Eliminates any possibility of incomplete mating



Compact size

Space saving for tight-packaging applications

Integral seal stopper with proven performance

Delivers IP67 rating; prevents ingress of dust and water to ensure reliable connection

Raised-body male terminal design

Provides polarization to prevent mis-mating



Spring-beam terminal design

Provides high pressure and small deflection for high-vibration applications

Markets and Applications

Automotive

Door electronics
Lamp mirrors
Mirror harnesses
Parking sensors
Powered rear-view mirrors
Switches
Wipers
Steering controls

Consumer

Washing machines
Vending machines
Water heaters
Air conditioners

Industrial / Industrial Automation

LED lighting



Automotive



Consumer Appliances

Off-The-Shelf Mizu-P25 (Mini Type) Cable Assemblies

molex

Specifications*

REFERENCE INFORMATION

Packaging: See product specs
UL File No.: E29179
Mates With: Mizu-P25 receptacle/plug
Terminals Used: Series 50147 and 50148
Designed In: millimeters
RoHS: Yes
Halogen-Free: No
V-O: Yes
Glow wire Compliant: No

ELECTRICAL

Voltage (max.): Up to 60V
Current (max.): Up to 4.0A
Contact Resistance: 10 milliohms
Dielectric Withstanding Voltage:
500V AC for 1 minute between adjacent terminals
Insulation Resistance (min.): 250 Megohms

PHYSICAL

Pitch: 2.50mm
Wire Gauge: 0.5 sq.mm
Housing: Polyester
Contact: Phosphor Bronze
Plating: Tin
Operating Temperatures: -40 to +105°C

MECHANICAL

Contact Insertion Force (max): 58.8N
Contact Retention to Housing (min): 29.4N
Mating Force: 49.0 N to 58.8N
(depending on number of circuits)
Unmating Force: 14.7 N to 49.0N
(depending on number of circuits)

*Information is based on Mizu-P25 connector specifications

Ordering Information

Series	Component	Circuits	Lengths (mm)
215310			
215311			
215312	Mizu-P25 (Mini Type) Cable Assemblies	2, 3 and 4	150, 300 and 600
215313			

Custom product	Description
Contact Molex	Mizu-P25 (Mini Type) Custom Cable Assemblies

www.molex.com/link/otscableassemblies.html

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.