Pico-Lock Wire-to-Board Connector System



Available in 1.00, 1.50 and 2.00mm pitch, Pico-Lock Wire-to-Board Connector System is ideal for applications requiring ultra-low profile, high-current and secure locking

Features and Advantages

Beveled header in pin design

Provides smooth mating and pin-andcontact protection

Top friction locks

Provide additional mating retention and visual mating assurance

Side positive locks

Ensure secure mating retention with additional space savings compared to top-style locks

Supports up to 6.5A current applications


Enables superior performance in compact design

Two types of crimp barrel

Allows wide range of wire gauge selection depending on customer needs

Ultra-low-profile mated height

Provides space savings



Pico-Lock 1.00mm and 1.50mm pitch Wire-to-Board Connectors

Wide robust-fitting nails (solder tabs)

Offer secure PCB retention and additional mechanical stability



Mating guide for polarization


Prevents mis-mating while guiding the housing into the header

> Ultra-low mated height of 2.60mm is less than half the height of other micro connectors

Enables customers to save valuable space

Side positive lock

Provides secure locking system and extra height advantage compared to competitors



Pico-Lock 2.00mm Pitch Wire-to-Board Connectors

Markets and Applications

Automotive

Industrial

Infotainment Smart meters Interior electronics Factory automation Heads-up display Power supplies

Control units Security/Surveillance devices

Black boxes Transformers

Consumer

Telecommunications/Networking

LED/LCD TVs Wireless modems

Notebook PCs Servers

Tablets Medical

Gaming equipment On-body health-monitoring

LED lightings systems

Heaters/fans



Automotive infotainment



Smart meters



Glucose monitor



Security cameras



Pico-Lock Wire-to-Board Connector System



Specifications

REFERENCE INFORMATION

Packaging:

Header (Embossed tape)

Housing (Bag)

Crimp Terminal (Reel)

Designed In: millimeters

RoHS: Yes

Halogen Free: Low-halogen

MECHANICAL

Housing (Positive Lock) Strength (min.): 1.00mm Pitch(min.): 5N (0.50kgf)

1.50mm Pitch(min.): 10N (1.02kgf)

2.00mm Pitch (min.): 19.8N (2.0kgf)

Crimp Terminal Retention Force (min.):

1.00mm: 4N

1.50mm: 6.7N

2.00mm: 9.8N

Durability (min.): 30 cycles

ELECTRICAL

Voltage (max.): 150V (1.00 and 1.50mm)

Voltage (max.): 250V (2.00mm) Current (max.): 3.5A per circuit

* see more detail at derating table Contact Resistance(max.): 20 milliohms

Dielectric Withstanding Voltage:

500V AC (rms) for 1 minute (1.00 and 1.50mm)

800V AC (rms) for 1 minute (2.00mm) Insulation Resistance(min.): 1000 Megohms

PHYSICAL

Housing/Header: Polyamide (PA), UL 94V-0, Black

Contact: Copper Alloy

Plating:

Contact Area — Gold (Au) Solder Tail Area — Gold (Au) Underplating — Nickel (Ni)

Operating Temperature: -40 to +105°C

*Derating table (For electrical specifications)

1.00mm Pitch Pico-Lock rated current (max.)

Wire Size	Current (A)			
(AWG)	2-Circuit	4-Circuit	6-Circuit	
28	2.5	2.0	1.5	
30	2.0	1.5	1.5	

1.50mm Pitch Pico-Lock rated current (max.)

Wire Size	Current (A)				
(AWG)	2-Circuit	4-Circuit	8-Circuit	12-Circuit	
24	3.5	3.0	2.5	2.5	
26	3.0	2.5	2.0	2.0	
28	2.5	2.0	2.0	1.5	
30	2.5	2.0	1.5	1.5	
32	2.0	1.5	1.5	1.0	

2.00mm Pitch Pico-Lock rated current (max.)

Wire Size	Current (A)				
(AWG)	2-Circuit	3-Circuit	4-Circuit	5-Circuit	6-Circuit
20	6.5	5.5	5.5	5.0	5.0
22	5.0	5.0	4.5	4.5	4.0
24	4.5	4.0	3.5	3.5	3.5
26	3.5	3.5	3.0	3.0	3.0

Notes:

- 1) Values are for reference only.
- 2) Current deratings are based on not exceeding 30°C temperature.
- 3) Temperature rise is measured in barrel area of crimp terminal.
- 4) PCB trace design can greatly affect temperature rise results.
- 5) Data is for all circuits powered.

Ordering Information

Pitch (mm)	Circuit Size	Applicable Wire Gauge (AWG)	Housing	PCB Header
2.00	2 to 6	20 to 26 (Terminal <u>205342</u>)	<u>205341</u>	<u>205338</u>
1.50	0 to 10	24 to 28 (Terminal <u>504052-0098</u>)	E040E1	<u>504050</u>
	2 to 12	30 to 32 (Terminal <u>504052-0298</u>)	<u>504051</u>	
1.00	2 to 6	28 to 30 (Terminal <u>503765</u>)	<u>503764</u>	<u>503763</u>

www.molex.com/link/picolock.html